


Actuator BD61



BD61 is a quiet and powerful actuator up to 5000N thrust, designed for furniture, home care and fitness equipment. The design of slider-type linear motion achieves a larger stroke with a smaller installation size, making BD61 one of the ideal driving solutions for electric recliner.

Content

Features and Options	3
Performance Data	4
Dimensions	6
1. Installation dimension	6
2. Drawing	6
3. Front connector	6
4. Rear connector	6
Compatibility	7
Cable Plug	8
Cable with Flying Leads	9
1. Basic, without positioning feedback.	9
2. With single Hall effect sensor for positioning	9
3. With dual Hall effect sensors for positioning	9
Ordering Key	10

Features and Options


- Main applications: Furniture, Home care, Fitness equipment
- Input voltage: 24V DC
- Max. load: 5000N (Push) / 3500N (Pull)
- Max. speed at no load: 16.1mm/sec (16mm pitch, refer to performance data)
- Speed at full load: 2.6mm/sec (4mm pitch @5000N loaded, refer to performance data)
- Stroke: 100~1000mm
- Noise level: ≤ 53 dB
- Preset limit switches
- Positioning:
 - Optional digital positioning feedback with dual Hall effect sensors
 - Optional digital positioning feedback with single Hall effect sensor
- Duty cycle: 10%, max. 2 min. continuous operation in 20 min.
- Operating ambient temperature: -20°C~+65°C
- Storage ambient temperature: -25°C~+65°C
- Optional Mechanical brake
- Optional Mounting bracket




Performance Data

Model No.	Push Max. (N)	Pull Max. (N)	* Typical speed (mm/s)		* Typical current (A)	
			No load	Full load	No load	Full load
BD61-XX- A4 -XXX.XXX-CXX-X	5000	3500	4.2	2.6	0.5	3.1
BD61-XX- A6 -XXX.XXX-CXX-X	4000	3000	6.3	4.3	0.5	2.7
BD61-XX- A8 -XXX.XXX-CXX-X	3000	2000	8.4	5.7	0.5	2.6
BD61-XX- AC -XXX.XXX-CXX-X	2000	2000	12.4	8.3	0.5	2.6
BD61-XX- AG -XXX.XXX-CXX-X	1500	1500	16.1	12.4	0.5	2.4

Speed VS. Load



Current VS. Load



Push / Pull Load (N) — Push Load (N) - - - -

Note:

* The typical speed or typical current means the average value neither upper limit nor lower limit, which measured under room temperature and stable power. The performance curves are made with typical values.



- **Inrush current**



- When the actuator starts to operate, an inrush current of about 0.2 seconds will be generated. The starting inrush current of BD61 can reach about 3 times of the typical current under the actuator load.
- If a circuit board power supply is used, the specifications must be sufficient to handle the inrush current. If batteries are used as the power source, inrush current will not be a problem.
- MOTECK controllers are designed to take into account the inrush current when the actuator starts. If the user provides his or her own controller, this feature must be considered in the specifications and protection mechanisms. Besides, the connectors, switches and relays selected by users must also be able to withstand the starting currents.





Dimensions

1. Installation dimension




- Retracted length (A) = 127mm Min. (± 3 mm)
- Available stroke (S) range = 100~1000mm
- Extended length (B) = Retracted length (A) + Stroke (S)

2. Drawing

- Standard




- With mounting bracket (Option)




3. Front connector

- 1: Plastic slider block



4. Rear connector

- 1: Plastic



Unit: mm



Compatibility

Product	Model	Application condition ⁽¹⁾	BD61 spec
Control box	T-control, CS1, CS2, CB3T, CB4M, CBT2	Max. 3A current per channel	• Without positioning sensor • With Moteck F-type DIN male plug
	CF11H, CF12H	Max. 3.6A current per channel	• Without positioning sensor • With Moteck L3-type minifit male plug
	CB3T-SY	Max. $\leq 5A$ current 2 channels	• With dual Hall effect sensors for positioning • With Moteck F-type DIN male plug
	CB4M-S, CB4M-B	Max. 3A current per channel	
	CF11S	Max. $\leq 6A$ current 2 channels	• With dual Hall effect sensors for positioning • With Moteck L3-type minifit male plug
	CF12S	Max. 3A current per channel	
Hand control	Depend on control box		• Powered by control box
	HS15, H2B, H2G, HB, TPSL, HS02, HZ02, HZ03, HZ04, HZ05, HZ06	Max. 3A current	• With Moteck S-type DIN 41529 male plug ⁽²⁾

Notes:






⁽¹⁾ If the current limit of the selected control box is lower than the typical current of the actuator model under full load, the actuator could not be operated in full performance.

⁽²⁾ The actuator's plug connects directly to the dedicated connection cable of these direct-cut hand controls. An external DC power supply is then connected to make them a direct-cut system, no control box.





Cable Plug

• Connecting control devices that provide power

	Without positioning feedback	Positioning feedback with dual Hall effect sensors
 Moteck F-type DIN male plug	 4p2c	 6p6c
 Moteck L3-type Minifit male plug	 6p2c	 6p6c
 Moteck S-type DIN 41529 male plug	 2p2c	N/A

Note: Pin definition

	Definition	Descriptions												
Power	M+	Connect M+ to "Vdc +" & M- to "Vdc -" of DC power to extend the actuator. Switch the polarity of DC input to retract it.												
	M-													
Signal	Vin	Voltage input range: 5~20V												
	Hall 1 output	High= Input - 1.2V (±0.6V) Low= GND Hall signal data: Actuator extends  Actuator retracts 												
	Hall 2 output	Hall effect sensor resolution: <table><tr><th>Model No.</th><th>Resolution (Pulses/mm)</th></tr><tr><td>BD61-XX-A4-XXX.XXX-CXX-HSX</td><td>10.0</td></tr><tr><td>BD61-XX-A6-XXX.XXX-CXX-HSX</td><td>6.667</td></tr><tr><td>BD61-XX-A8-XXX.XXX-CXX-HSX</td><td>5.0</td></tr><tr><td>BD61-XX-AC-XXX.XXX-CXX-HSX</td><td>3.333</td></tr><tr><td>BD61-XX-AG-XXX.XXX-CXX-HSX</td><td>2.5</td></tr></table>	Model No.	Resolution (Pulses/mm)	BD61-XX-A4-XXX.XXX-CXX-HSX	10.0	BD61-XX-A6-XXX.XXX-CXX-HSX	6.667	BD61-XX-A8-XXX.XXX-CXX-HSX	5.0	BD61-XX-AC-XXX.XXX-CXX-HSX	3.333	BD61-XX-AG-XXX.XXX-CXX-HSX	2.5
	Model No.	Resolution (Pulses/mm)												
BD61-XX-A4-XXX.XXX-CXX-HSX	10.0													
BD61-XX-A6-XXX.XXX-CXX-HSX	6.667													
BD61-XX-A8-XXX.XXX-CXX-HSX	5.0													
BD61-XX-AC-XXX.XXX-CXX-HSX	3.333													
BD61-XX-AG-XXX.XXX-CXX-HSX	2.5													
GND														



Cable with Flying Leads



1. Basic, without positioning feedback.

	Wire color	Definition	Descriptions
Power wires	White	DC Power	Connect white wire to "Vdc +" & black wire to "Vdc -" of DC power to extend the actuator. Switch the polarity of DC input to retract it.
	Black		

2. With single Hall effect sensor for positioning

	Wire color	Definitions	Descriptions												
Power wires	Blue	DC Power	Connect blue wire to “Vdc +” & brown wire to “Vdc -“ of DC power to extend the actuator. Switch the polarity of DC input to retract it.												
	Brown														
Signal wires	Yellow	Vin	Voltage input range: 5~20V												
	Red	Hall output	High= Input - 1.2V (±0.6V) Low= GND Hall signal data:  Hall effect sensor resolution: <table><tr><th>Model No.</th><th>Resolution (Pulses/mm)</th></tr><tr><td>BD61-XX-A4-XXX.XXX-CXX-HSX</td><td>10.0</td></tr><tr><td>BD61-XX-A6-XXX.XXX-CXX-HSX</td><td>6.667</td></tr><tr><td>BD61-XX-A8-XXX.XXX-CXX-HSX</td><td>5.0</td></tr><tr><td>BD61-XX-AC-XXX.XXX-CXX-HSX</td><td>3.333</td></tr><tr><td>BD61-XX-AG-XXX.XXX-CXX-HSX</td><td>2.5</td></tr></table>	Model No.	Resolution (Pulses/mm)	BD61-XX-A4-XXX.XXX-CXX-HSX	10.0	BD61-XX-A6-XXX.XXX-CXX-HSX	6.667	BD61-XX-A8-XXX.XXX-CXX-HSX	5.0	BD61-XX-AC-XXX.XXX-CXX-HSX	3.333	BD61-XX-AG-XXX.XXX-CXX-HSX	2.5
			Model No.	Resolution (Pulses/mm)											
			BD61-XX-A4-XXX.XXX-CXX-HSX	10.0											
BD61-XX-A6-XXX.XXX-CXX-HSX	6.667														
BD61-XX-A8-XXX.XXX-CXX-HSX	5.0														
BD61-XX-AC-XXX.XXX-CXX-HSX	3.333														
BD61-XX-AG-XXX.XXX-CXX-HSX	2.5														
Black	GND														

3. With dual Hall effect sensors for positioning

	Wire color	Definitions	Descriptions												
Power wires	Blue	DC Power	Connect blue wire to “Vdc +” & brown wire to “Vdc -“ of DC power to extend the actuator. Switch the polarity of DC input to retract it.												
	Brown														
Signal wires	Yellow	Vin	Voltage input range: 5~20V												
	Red	Hall 1 output	High= Input - 1.2V (±0.6V) Low= GND Hall signal data:  Actuator extends  Actuator retracts												
	Green	Hall 2 output	Hall effect sensor resolution: <table><thead><tr><th>Model No.</th><th>Resolution (Pulses/mm)</th></tr></thead><tbody><tr><td>BD61-XX-A4-XXX.XXX-CXX-HSX</td><td>10.0</td></tr><tr><td>BD61-XX-A6-XXX.XXX-CXX-HSX</td><td>6.667</td></tr><tr><td>BD61-XX-A8-XXX.XXX-CXX-HSX</td><td>5.0</td></tr><tr><td>BD61-XX-AC-XXX.XXX-CXX-HSX</td><td>3.333</td></tr><tr><td>BD61-XX-AG-XXX.XXX-CXX-HSX</td><td>2.5</td></tr></tbody></table>	Model No.	Resolution (Pulses/mm)	BD61-XX-A4-XXX.XXX-CXX-HSX	10.0	BD61-XX-A6-XXX.XXX-CXX-HSX	6.667	BD61-XX-A8-XXX.XXX-CXX-HSX	5.0	BD61-XX-AC-XXX.XXX-CXX-HSX	3.333	BD61-XX-AG-XXX.XXX-CXX-HSX	2.5
	Model No.	Resolution (Pulses/mm)													
	BD61-XX-A4-XXX.XXX-CXX-HSX	10.0													
BD61-XX-A6-XXX.XXX-CXX-HSX	6.667														
BD61-XX-A8-XXX.XXX-CXX-HSX	5.0														
BD61-XX-AC-XXX.XXX-CXX-HSX	3.333														
BD61-XX-AG-XXX.XXX-CXX-HSX	2.5														
Black	GND														



Ordering Key

		BD61- 24 - AG - 135 - 1135 - C 1 1 - HS2 - BK - 1										
Input voltage	24: 24V DC											
Motor and Spindle type	A4: 2500rpm / 4mm pitch A6: 2500rpm / 6mm pitch A8: 2500rpm / 8mm pitch AC: 2500rpm / 12mm pitch AG: 2500rpm / 16mm pitch											
Retracted length (Refer to Page 6)	XXX											
Extended length (Refer to Page 6)	XXXX											
Front connector (Refer to Page 6)	1: Plastic slider block											
Rear connector (Refer to Page 6)	1: Plastic											
Positioning feedback	Blank: None HS1: Hall effect sensor x 1 HS2: Hall effect sensor x 2											
Option (Multiple choice is allowed)	Blank: None BK: Mechanical brake L: Mounting bracket											
Cable	0: 300mm straight 1: 1000mm straight 2: 450mm with 300mm coiled											

Terms of Use

The user is responsible for application suitability of Moteck products. As ongoing improvement process continues, products listed on the Moteck website are subject to change without prior notice. Moteck reserves the right to terminate the sales or remove any product displayed on the website, or listed in its catalogues.

